

HANDSHOWER
K-R33032T

Features

- Environmentally friendly materials.
- Easily transition between sprays with push buttons.
- 2-function handshower.
- WaterMind Technology, innovatively designs the nozzle, automatically adapts to water pressure, ensuring consistent water performance.
- Microbubble spray, deeply cleansing the oil and dirt from the scalp and body skin.
- Vitamin C filter, effectively removes residual chlorine from the water, providing delicate care for skin and hair.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552
- GBT 23447-2023

Installation Notes


Install this product according to the installation guide.



Specified Model

Model	Description	Color/Finishes
K-R33032T	Spacity 2F handshower	Others


For a full range of color finishes in your market please contact your local Kohler representative



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

หัวฝักบัวสายอ่อน
K-R33032T

คุณลักษณะ

- ใช้วัสดุที่เป็นมิตรต่อสิ่งแวดล้อม
- เปลี่ยนรูปแบบสายน้ำได้ง่ายด้วยปุ่มกด
- หัวฝักบัวปรับสายน้ำได้ 2 รูปแบบ
- สายน้ำแบบฝนพร้อมเทคโนโลยี WaterMind ขนาดรูน้ำออกปรับโดยอัตโนมัติ เพื่อประสิทธิภาพการไหลของน้ำที่สม่ำเสมอ
- สายน้ำไมโครบับเบิล ชำระล้างสิ่งสกปรกจากผิวได้อย่างล้ำลึก
- มาพร้อมไส้กรองวิตามินซี ช่วยขจัดคลอรีนตกค้าง เพื่อการดูแลผิวและเส้นผมอย่างอ่อนโยน

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552
- GBT 23447-2023

ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง



รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-R33032T	หัวฝักบัวสายอ่อน รุ่นสเปซซีดี	สีอื่น ๆ

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน




กราฟแสดงอัตราการไหล

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)

หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์