




33627T-NA 去水弯管转接头	
安装之前	BEFORE YOU BEGIN
所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。 说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。 注意事项： 1. 遵守当地管路安装条例。 2. 关闭主供水源。 3. 要求预置的地面或墙面排水管外径须为50mm，且排水管高出地面或凸出墙面至少35mm，方能安装此接头产品。	All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice. Please leave these instructions for the consumer. They contain important information. NOTES: 1. Observe all local plumbing codes. 2. Shut off the main water supply. 3. To install this product, the floor or wall drain pipe with outer diameter 50mm should be prearranged, and the drain pipe must protrude at least 35mm above the floor or wall surface.
安装尺寸	ROUGH-IN DIMENSIONS
	
安装步骤	INSTALLATION
安装排水管(1，用户自备)，确保外径须为50mm的排水管高出地面或凸出墙面至少35mm。 依次将螺母(2)、垫圈(3)和垫圈(4)套在排水管上，将排水内芯(5)插入排水管内，接着将连接件(6)安装到排水管上，并用螺母(2)将其拧紧。 依次将螺母(7)、垫圈(8)和垫圈(9)套入软管(10，用户自备)，将软管(10)插入连接件(6)内，并用螺母(7)将其拧紧。 安装完成后状态如图所示。	Install the drain pipe(1, not provided), ensure the floor or wall drain pipe with outer diameter 50mm should protrude at least 35mm above the floor or wall surface. Slide the nut(2), gasket(3) and gasket(4) onto the drain pipe in sequence, insert the drain core(5) into the drain pipe, and then install the joint(6) onto the drain pipe and tighten it with the nut(2). Slide the nut(7), gasket(8) and gasket(9) onto the hose(10, not provided) in sequence, insert the hose(10) into the joint(6), and tighten it with the nut(7). After installation, the status is shown in the figure.
	

安装结果检查	INSTALLATION CHECKOUT
检查并确保所有的衔接螺帽都已拧紧。打开排水器和主供水源，检查并修理有漏水的接口。	Ensure all coupling nuts are tightened. Turn on drain and water supply, check for leaks. Repair as needed.
质量担保	WARRANTY
科勒对正常使用下制造和质料上的瑕疵提供长达三年的质量担保，对其后出现的损坏不负任何责任。 注意：担保范围不包括：环境温度低于0°C，外观碰伤，使用或清洗不当以及未按说明书安装的额外损伤；未有列明的修理和零件以及安装费用。 要获得担保服务，请通过您的安装承建者，或写信给科勒中国客户服务中心(请出示销售发票原件作为购货凭证)： 科勒(中国)投资有限公司中央客户服务中心 中国上海市静安区江场三路158号 邮编：200436 免费咨询保修电话：8008202628 & 4008202628 网址：www.kohler.com.cn	Kohler provides three years warranty for its defects of material & workmanship free during normal use from the date of the product is purchased. NOTES: This warranty does not cover problems arising from environment temperature below 0°C, surface damage, improper use, care or improper cleaning. Kohler is not responsible for labor charges, installation, or other incidental or consequential costs. To obtain warranty service, please contact your distributor, plumbing contractor or write to the following Kohler Customer Service Center (Please provide all pertinent information regarding your claim, including the original invoice, a complete description of the problem ect.): Central Customer Service Center, Kohler China Investment Co., LTD. NO.158 Jiang Chang San Road, Jing'an District, Shanghai, PRC Post Code: 200436 Toll-free service call: 8008202628 & 4008202628 Website: www.kohler.com.cn
清洗说明	CLEANING INSTRUCTIONS
适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净的软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。 有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。	All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning. Do not use abrasive cleaners or solvents on Kohler faucets and fittings.
零件图	SERVICE PARTS
 **订购时请说明颜色编号 **Color code must be specified when ordering	