


安装步骤

INSTALLATION



根据安装尺寸和胀塞(1)直径在墙面上适当的高度打两个孔，两孔之间距离如图所示。将胀塞分别塞入孔中。

用螺钉(2)锁紧底座(3)。底座安装方向如图所示。

将花洒托架(4)按住按钮从滑杆(5)顶部或底部装入右侧槽。花洒支架高度根据用户需求调整。

将滑杆挂在底座上，用六角扳手(6)锁紧螺钉(7)以固定滑杆。

将盖(8)扣到滑杆上。

Select a suitable location to drill two holes on the finished wall according to the rough-in dimensions and diameter of the anchors(1), their distance is as shown in the figure. Press the anchors into the holes.

Tighten the bases(3) with the screws(2). The installation direction of the base is shown in the figure.

Press and hole the button on the shower bracket(4) and slide it into the right slot from the top or bottom of the slide bar(5). The height of the bracket is adjusted according to user needs.

Install the slide bar to the bases. Tighten the screws(7) with hex wrench(6) in order to secure the slide bar.

Press the caps(8) into each end of the slide bar.

清洗说明

CLEANING INSTRUCTIONS

适用于所有加工处理过的表面：以中性肥皂水清洗镀层表面，再以干净软布彻底擦干整个表面，许多清洁剂，比如氨水、去污粉及洁厕灵等，会对电镀表面造成伤害，切忌使用。

有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。


All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.

KOHLER®
SERVICE PARTS
零件图

随心雨
RAIN DUET
Slide Bar

38648T 60cm滑动花洒支架
38649T 80cm滑动花洒支架
38650T 100cm滑动花洒支架



**订购时请说明颜色编号
**Color code must be specified when ordering