

Features

- Brass construction.
- Leak-free ceramic disc valve with lifetime warranty.
- Durable Kohler finishes resist corrosion and tarnishing.
- Flexible G1/2" supply hoses for easy installation.
- 222 mm spout reach.
- 2 function pulldown spray.
- Faucet spout swivel 360° degree.
- Optimized integration of the pull-out hose and connector reduces assembly parts and simplifies installation.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2067-2552
- GB 18145-2014

Installation Notes

Install this product according to the installation guide.


PULL DOWN KITCHEN FAUCET
K-21366T-B4 / K-21367T-B4



Specified Model

Model	Description	Colors/Finishes	
K-21366T-B4	Taul pull down kitchen faucet	☐ CP: Polished	
K-21367T-B4	Taul pull down kitchen faucet	☐ CP: Polished Chrome	☐ Others

For a full range of color finishes in your market please contact your local Kohler representative.



Note: Flow rate are approximate. (1 gallon = 3.758 liters, 1 bar = 14.5 psi)

Unit: mm



Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- วัสดุเคลือบผิวพิเศษจากโคห์เลอร์ คงทน เงางาม
- สายน้ำขนาด G1/2"
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 222 มม.
- หัวฉีดแบบดึงออกได้ ปรับสายน้ำได้ 2 ระดับ
- คอกก๊อกหมุนได้ 360°
- สายน้ำดีที่ต่อเข้าสายหัวฉีดมาพร้อมข้อต่อในตัว ลดชิ้นส่วนประกอบและติดตั้งง่าย

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2067-2552
- GB 18145-2014

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง


ก๊อกผสมอ่างล้างจานชนิดหัวฝักบัว K-21366T-B4 / K-21367T-B4



รุ่นผลิตภัณฑ์



รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว	
K-21366T-B4	ก๊อกผสมอ่างล้างจานชนิดหัวฝักบัว รุ่นทอ	☐ CP: สีโครมเงา	
K-21367T-B4	ก๊อกผสมอ่างล้างจานชนิดหัวฝักบัว รุ่นทอ	☐ CP: สีโครมเงา	☐ อื่นๆ

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน



หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.758 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง
ภาพแสดงผลิตภัณฑ์