KOHLER®

SAN SOUCI

ONE-PIECE TOILET WITHOUT SEAT

K-21865ID-NS

Features

- Vitreous china.
- Elongated bowl.
- Includes polished chrome trip lever.
- Revolution 360 flushing system.
- Dual flush 3/4.8 liter per flush.
- 305 mm rough-in for S-trap.
- 698 x 418 x 619 mm



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1
- SNI 03-0797: 2006

Technical Information

Fixture:	
Configuration	one-piece, elongated
Water per flush	3/4.8 liter
Passageway	49 mm
Water area	180 x 155 mm
Water depth from rim	165 mm
Seat post hole centers	140 mm

Included Components:	
Tank cover	1343587-SP-**
Wax ring	1270224-SP
Shut off valve, G1/2” x G1/2”	1552114-SP-**
Water supply hose, stainless	1548548-SP
Hardware Kit	1156481-SP

Installation Notes

Install this product according to the installation guide.

Specified Model


Model	Description	Colors/Finishes
K-21865ID-NS	San Souci one-piece toilet, S-trap without seat	0: White

Call Center: 0-2700-9299
kohler.com


KOHLER®

SAN SOUCI

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)
Unit: mm



For plastic connector installation



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

Call Center: 0-2700-9299
kohler.com