

Features

- Brass construction.
- Durable Kohler finishes resist corrosion and tarnishing.
- Adjustable inlet fittings with 15 mm tolerance.
- Optimized sprayface with Katalyst® Air-induction for improved water coverage.
- Precise thermostatic temperature control with over-ridable temperature stop.
- Includes 1-function showerhead.
- Includes 3-function handshower with WaterMind technology.

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552
- QB 2806-2017
- GB/T 23447-2023

Installation Notes

Install this product according to the installation guide.


SHOWER COLUMN
K-73111T-B7




Specified Model

Model	Description	Colors/Finishes	
K-73111T-B7	Composed 3-Way thermostatic shower column	CP: Polished Chrome	Others


For a full range of color finishes in your market please contact your local Kohler representative.



Flow Curve - Showerhead




Flow Curve - Handshower



Flow Curve - Bath Outlet

Note: Flow rate are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- วาล์วเคลือบผิวพิเศษจากโครโมเลอร์ คงทน เงางาม
- อุปกรณ์ติดตั้งกับท่อน้ำเข้าปรับระยะได้ 15 มม.
- หัวฝักบัวระบบแคตทาลิส เทคโนโลยีการอัดอากาศเพื่อสายนํ้าชุ่มฉ่ำเต็มสัมผัส
- ระบบเทอร์โมสแตตติกควบคุมอุณหภูมิแม่นยำ พร้อมด้วยตัวหยุดนิรภัย
- พร้อมหัวฝักบัวก้านแข็ง 1 ระดับ
- พร้อมฝักบัวสายอ่อนเทคโนโลยีวอเตอร์ไมด์ ปรับสายนํ้าได้ 3 รูปแบบ

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552
- QB 2806-2017
- GB/T 23447-2023

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

ก๊อกผสมเย็นอาบลงอ่างพร้อม
ชุดฝักบัวสายอ่อนและชุดฝักบัวก้านแข็ง




K-73111T-B7



รุ่นผลิตภัณฑ์


รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว	
K-73111T-B7	ก๊อกผสมเย็นอาบลงอ่างระบบเทอร์โมสแตตติกพร้อมชุดฝักบัวสายอ่อนและชุดฝักบัวก้านแข็ง รุ่นคอมโพส	CP: สีโครมเงา	สีอื่นๆ

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโครโมเลอร์ในประเทศของท่าน



หมายเหตุ : อัตราการไหลโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์