


SLIDING,SS,L BYPASS,W/SC, 10mm  
L型双移门, 缓冲, 防爆贴膜玻璃, 10mm  
K-22318T

SLIDING,SS,L BYPASS, 10mm  
L型双移门, 防爆贴膜玻璃, 10mm  
K-701532T

SLIDING,SS,L BYPASS,8mm  
L型双移门, 防爆贴膜玻璃, 8mm  
K-701538T

### K-22318T




\* Color code must be specified when ordering.  
\* 订购时请说明颜色编号

SLIDING,SS,L BYPASS,W/SC, 10mm  
L型双移门, 缓冲, 防爆贴膜玻璃, 10mm  
K-22318T

SLIDING,SS,L BYPASS, 10mm  
L型双移门, 防爆贴膜玻璃, 10mm  
K-701532T

SLIDING,SS,L BYPASS,8mm  
L型双移门, 防爆贴膜玻璃, 8mm  
K-701538T

K-701532T  
K-701538T



\* Color code must be specified when ordering.  
\* 订购时请说明颜色编号

SLIDING,SS,L BYPASS,W/SC, 10mm  
L型双移门, 缓冲, 防爆贴膜玻璃, 10mm  
K-22318T

SLIDING,SS,L BYPASS, 10mm  
L型双移门, 防爆贴膜玻璃, 10mm  
K-701532T

SLIDING,SS,L BYPASS,8mm  
L型双移门, 防爆贴膜玻璃, 8mm  
K-701538T

P/N 零件号	DESCRIPTION 描述		COLOR 颜色	
★ 1291696-*	Door Glass, Inner 10mm 门玻璃 (内) 10mm		FM, IC	
★ 1291697-*	Door Glass, Outer 10mm 门玻璃 (外) 10mm			
★ 1291694-*	Door Glass, Inner 8mm 门玻璃 (内) 8mm			
★ 1291695-*	Door Glass, Outer 8mm 门玻璃 (外) 8mm			
★ 1361203-*	Side Panel Glass 10mm 侧门玻璃 10mm			
★ 1269958-*	Side Panel Glass 8mm 侧门玻璃 8mm			
1291195-*	SS Top Rail Assy 不锈钢上轨道组件		S, AF, RGD	
1361236-*	SS Bottom Rail Assy L型不锈钢下轨道组件		S, AF, RGD	
1291215-*	Side Panel, Bypass, Skyline SS 侧固横梁		S, AF, RGD	
1291216-*	SS Wall, Side Panel, Bypass, Skyline SS 侧固墙材		S, AF, RGD	
★ 1291211-L-*	SS Wall Jamb, LH 不锈钢墙材 (左)		S, AF, RGD	
★ 1291211-R-*	SS Wall Jamb, RH 不锈钢墙材 (右)		S, AF, RGD	
★ 1291214-L-*	SS Corner Post, LH 双移转角竖材 (左)		S, AF, RGD	
★ 1291214-R-*	SS Corner Post, RH 双移转角竖材 (右)		S, AF, RGD	
1291231-*	SS Wall Top Cap, Side Panel, Bypass, Skyline SS 侧固顶盖		S, AF, RGD	
1291229-*	SS Wall Top Cap, Bypass, Skyline SS 不锈钢双移门顶盖		S, AF, RGD	
1291230-*	SS Corner Post Top Cap, Bypass, Skyline SS 转角顶盖		S, AF, RGD	
1361224	Bottom Corner Fixed Part 下转角固定件		S, AF, RGD	
★ 1291228	Buffer Block, Bypass 缓冲锁块			
★ 1361159-*	Top Roller Assy, Skyline SS, Bypass 不锈钢双移门上缓冲轮组		S, AF, RGD	
★ 1291234	No-Rebound Assy, Bypass, Skyline SS 不锈钢双移门防撞块			
★ 1361164-*	Top Roller Assy, Bypass, 10mm 不锈钢双移门上轮组 10mm		S, AF, RGD	
★ 1361162-*	Bottom Roller Assy, Long, 10mm 不锈钢双移门下轮组 (长) 10mm		S, AF, RGD	
★ 1361163-*	Bottom Roller Assy, Short, 10mm 不锈钢双移门下轮组 (短) 10mm		S, AF, RGD	
★ 1291222-*	Top Roller Assy, Bypass, 8mm 不锈钢双移门上轮组 8mm		S, AF, RGD	
★ 1291217-*	Bottom Roller Assy, Long, 8mm 不锈钢双移门下轮组 (长) 8mm		S, AF, RGD	
★ 1291218-*	Bottom Roller Assy, Short, 8mm 不锈钢双移门下轮组 (短) 8mm		S, AF, RGD	
★ 1210838-*	Side Metal Handle, Skyline 新乐单装拉手		S, AF, RGD	
▲ 1361230	New SS Bypass Seal Strip Package 8mm 新乐双移带固玻 8mm 密封配件包	★ 1361246	Insert Seal, Skyline SS, Bypass 8mm 不锈钢双移门嵌入胶条 8mm	
		★ 1157901	Insert Seal 8mm 单边胶条 8mm	
▲ 1361231	New SS Bypass Seal Strip Package 10mm 新乐双移带固玻 10mm 密封配件包	★ 1361247	Insert Seal, Skyline SS, Bypass 10mm 不锈钢双移门嵌入胶条 10mm	
		★ 1157883	Insert Seal 10mm 单边胶条 10mm	
▲ 1361229	New SS Bypass SPP 新乐双移 - 维修配件包	1291249	Spanner, Bypass, Skyline SS 上轮调节工具	
		1361220-*	Screw M4X10 上滑轮装饰盖 M4X10	S, AF, RGD
		1361239	Screw M4X10 十字沉头不锈钢机制 M4X10	
		1150121	Screw ST3.5X40 盘头自攻螺钉 ST3.5X40	
		1057064	Hollow Wall Anchor, Nylon 膨胀套	
		1078843	Screw Key 2mm 内六角扳手 (加长) 2mm	
		1095457	Screw Key 3mm 内六角扳手 3mm	

SLIDING,SS,L BYPASS,W/SC, 10mm  
L型双移门, 缓冲, 防爆贴膜玻璃, 10mm

K-22318T

SLIDING,SS,L BYPASS, 10mm  
L型双移门, 防爆贴膜玻璃, 10mm

K-701532T

SLIDING,SS,L BYPASS,8mm  
L型双移门, 防爆贴膜玻璃, 8mm

K-701538T

Note: Components marked in ▲ can only be ordered in whole pack. When ordering components marked in ★, customers need provide measurement form and corresponding product SKU.

注意: 带▲标注零件仅可整包订购, 带★标注零件订购时需附加测量单和产品SKU号。

Glass options: L1, L3, L4, L5, L8, L9, C, MZ, IC

玻璃花纹可供选择: L1, L3, L4, L5, L8, L9, C, MZ, IC

FM-It is for filmed glass. The following decorative patterns can be chosen (refer to the table below) together with FM glass.

IC-It is for laminated glass with easy clean coating. The following decorative patterns cannot be chosen together with IC glass.

FM- 此号码为防爆膜玻璃, 配备FM时, 可以选择以下指定花纹代码(参考下表)。

IC- 此号码为夹层+超净玻璃, 配备IC时, 以下代码不能再选择。

Refer to the table below for glass options

玻璃选项参考下表

P/N 零件号	DESCRIPTION 描述
1291888-L1	蕾丝花纹, L1
1291888-L3	思绪花纹, L3
1291888-L4	梅玛花纹, L4
1291888-L5	晨雾花纹, L5
1291888-L8	繁星花纹, L8
1291888-L9	丝雨花纹, L9
1291888-MZ	镜面玻璃, MZ
1291888-C	超净玻璃, C
1291888-IC	夹胶超净, IC