



Harken™
One-piece elongated toilet with skirted trapway,
dual-flush
K-22695T-S

Features


- One-piece toilets integrate the tank and bowl into a seamless, easy-to-clean design
- Elongated bowl offers added room and comfort
- Rim-to-floor height: 15-9/16" (395 mm)
- Dual-flush offers a choice of 1.0 or 1.28 gpf (3.3 or 4.8 lpf)
- Left-hand Vibrant Brushed Bronze trip lever
- 1-15/16" (49 mm) fully glazed trapway
- Revolution 360™ flushing technology generates a forceful swirling motion to keep the bowl clean longer
- French Curve™ Quiet-Close™ seat closes quietly and quickly unlatches from the toilet for easy removal and convenient cleaning
- Quick-Attach™ hardware for fast and secure installation

Material

- Vitreous china

Installation

- Floor-mount
- Standard 12" (305 mm) rough-in
- Supply line sold separately




Codes/Standards

None Applicable

See website for detailed warranty information.

KOHLER®

Harken™
One-piece elongated toilet with skirted trapway,
dual-flush
K-22695T-S



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Flush type:	Class Five
Trap passageway:	1-15/16" (49 mm)
Water surface size:	7-1/2" x 5-3/8" (191 mm x 136 mm)
Rim to water surface:	6-7/16" (164 mm)

Notes

Install this product according to the installation instructions.