

**Sculpt Series Hanging Mirror**  
**YM2040SPPFN3H Illuminated Pill Specification Sheet**

**FEATURES**

- Perimeter light pattern
- Pill shaped mirror with a hand finished metal frame
- Ceiling mounted for unique installations
- Accommodates up to 11' high and lofted ceilings (up to 45°)

Kelvin	3000K
CRI	90+
R9 Value	50+
Delivered Lumens	650

**ELECTRICAL FEATURES**

- Compatible with most Triac/Phase-cut dimmers
- Dimmable LED task lighting to 1%
- Operates on 120V 0.80A Max per Power Supply
- Total power use - 40W

**MATERIALS & CONSTRUCTION**

- Stainless steel frame
- Includes all required mounting hardware
- Requires ceiling fan electrical box (rated for 50 lb min)


**CODES & STANDARDS**

Sculpt Illuminated Hanging Mirror is certified to:

- UL 1598
- CSA Standard C22.2 No. 250.0

**DIMENSIONS**

- Width: 19-1/4" (489 mm)
- Height: 39-3/8" (1000 mm)
- Depth: 1-7/8" (47 mm)
- Install: 47-3/8" (1203 mm) - 93-3/8" (2372 mm)




**MODEL NUMBER KEY**

PRODUCT LINE	WIDTH	HEIGHT	SHAPE	LIGHT PATTERN	FINISH	SHAPE	OPTIONS
YM = Sculpt Mirror	20	40	S = Pill	P = Perimeter	PF = 1/2" Frame	N 3 = 3000K	H = Ceiling Mounted

**OPTIONS**

- Available in:
  - YM2040SPPFN3H83 - Matte Black
  - YM2040SPPFN3H84 - Polished Stainless Steel
  - YM2040SPPFN3H86 - Brass

**MORE INFORMATION**



Scan the QR code to see the details found in the Sculpt Hanging Mirror installation instructions.

Use the camera app on your mobile device to look at this QR code. This will allow you to quickly access web pages and other relevant documents.

