

## AIO Reserve Cabinet AR3048D4FP2LP Cabinet Specification Sheet

### FEATURES

- Perimeter task light pattern
- Integrated dimmable and tunable light controls
- Modular - combine multiple cabinets, lighting, or mirrors
- Mirrored interior with eight adjustable, cantilevered glass shelves, adjustable in 1" increments
- Includes installation hardware for recess mounting
- Includes push-to-open door mechanism (VT-PUSHKIT)

Kelvin	2700K - 5600K
CRI	90+
R9 Value	50+
Delivered Lumens	2617

### ELECTRICAL FEATURES

- Standard knock out for 1/2" (13mm) cable connector
- Wired Internally - Front access serviceability
- Two standard 110V outlets in the vertical column
- One 5A USB/110V combination outlet - USB-C & USB-A
- Automatic integrated vertical interior LED lighting
- Includes Wire Organizer (VT-WIREORG), and Illuminated Sliding Pull-Out Mag Mirror (VT-SPOMM-L)


### CONSTRUCTION

- Blum 110° slow close hinges
- Rust free Satin anodized aluminum construction
- 3 mirror design - cabinet interior and both sides of door
- Safeseal® Gasket with sealed corners on cabinet body

### DIMENSIONS


- Width: 29-1/4" (743 mm)
- Height: 48" (1219 mm)
- Depth: 4-5/8" (118 mm) When surface mounted  
15/16" (23 mm) When recessed

### MORE INFORMATION




Scan the QR code to see the rough opening and electrical details found in the AIO Reserve cabinet installation instructions.


Use the camera app on your mobile device to look at this QR code. This will allow you to quickly access web pages and other relevant documents.



#### Included Accessories:



VT-SPOMM-L



HT-ORGKIT



VT-PUSHKIT



VT-WIREORG



HT-MAGORG

### MODEL NUMBER KEY

PRODUCT LINE	WIDTH	HEIGHT	DEPTH	MIRROR OPTIONS	DOOR OPTIONS	HINGE SIDE	LIGHT STYLE
AR	30	48	D4	FP = Polished Edge	2 = Two Door	L = Large LH Door	P = Perimeter

**OPTIONS**

- Other widths / heights / light patterns available
- Assorted glass bins:
  - Medium (GLASSBIN5.25)
  - Large (GLASSBIN8.5)
- Storage accessories supplied with cabinet, also available separately: HT-MAGORG, HT-ORGKIT, HT-STORAGETRAY, VT-WIREORG, VT-SPOMM-L


**CODES & STANDARDS**

Electric Option Models are ETL certified to:


- UL 962
- CSA Standard C22.2 No. 68

**INSTALLATION OPTIONS**


- Compatible Mounting Kits (Single Cabinet):
  - Surface Mount Kit (P2SMKIT48D4P)
- Pairs with Modular mirrors
- Gangs to M-Series Reserve Cabinet via:
  - Surface Mount Ganging Kit (P2SM-GKIT48D4P)
  - Recessed Ganging Kit (P2RMGKIT)
- Compatible with Vesper, Tenor, InLine, and Profiles Lights
- Compatible with M Reserve, Presence, M Series, Profiles, PL Series, PL Portray, AiO, and Vitality Cabinets
- **Recessed Mount Rough Opening:**  
**28-1/2" W x 47-1/4" H (724 mm W x 1201 mm H)**



Front View



Recessed Mount



Surface Mount