

Features

- Ergonomic and Straight line design suitable for compact rooms with deck space.
- Made of our highly durable material (much harder than ordinary ceramic).
- Stain- Resistant coating keeps it shiny and makes it easy to clean.
- Optimum Depth to contain Splashes.

Product Details

- Material: Vitreous China
- Overflow: Without Overflow Hole

Recommended Accessories

- Bottle Trap (75823IN-**).
- Compatible Drain (20746IN-**).



SKU Codes	Description
72288IN-4-**	Aleo Single Control Pillar Lavatory Faucet
72275IN-4-**	Aleo Lavatory Faucet
72326IN-4-**	Aleo+ Single Control Pillar Lavatory Faucet
72312IN-4-**	Aleo+ Lavatory Faucet
99452IN-4-**	Kumin® Pillar Lavatory Faucet
98827IN-4ND-**	Kumin® Lavatory Faucet
74028IN-4-**	Taut™ Pillar Lavatory Faucet
74013IN-4-**	Taut™ Lavatory Faucet
22538IN-4-**	Hone® Pillar Faucet
22534IN-4ND-**	Hone® Lavatory Faucet
26042IN-4-**	Beam Pillar Faucet
26040IN-4ND-**	Beam Lavatory Faucet
23482IN-4-**	Parallel™ Pillar Faucet
23472IN-4ND-**	Parallel™ Lavatory Faucet
24847IN-4-**	Elate® Pillar Faucet
24844IN-4ND-**	Elate® Lavatory Faucet
23968IN-4-**	Vive Pillar Faucet
23966IN-4ND-**	Vive Lavatory Faucet
16027IN-4ND-**	July® Lavatory Faucet
16312IN-4-**	JULY® Pillar Lavatory Faucet

**-Finish code must be specified when ordering.


KOHLER® Ten-Year Limited Warranty

See website for detailed warranty information
www.kohler.co.in/warranty

Available Colour/Finishes

Colour tiles intended for reference only.

Colour	Code	Description
	0	White



Technical Specification

All product dimensions are nominal.

Lavatory configuration	Single
Installation	Wall-Mount
Lav area	Length: 15 7/8" (40.3cm) Width: 22 5/16" (56.7cm) Height: 6 3/4" (17.2 cm)
Drain hole	Ø1 3/4" (4.4cm)
Template	1382340-IN2

Notes

Install this product according to the installation guide.

Choose a faucet that will provide adequate clearance and will direct the water stream to the center of the bathroom sink.