



## Southaven®

33" top-mount single-bowl kitchen sink  
**37047-4**

### Features

- Four faucet holes
- 9-1/4" (235 mm) depth provides generous workspace
- 3-5/8" (92 mm) drain opening
- Stainless steel with luster bowl finish and a satin deck finish

### Material

- Premium 18-gauge stainless steel

### Installation

- Top-mount

### Recommended Products/Accessories

7400 Stainless Steel Sink Drain and Strainer  
K-23726 Drain treatment  
K-23729 Stainless steel cleaner

### Included Components

1279210 12 Count Installation Clips



### Codes/Standards

ASME A112.19.3/CSA B45.4

### STERLING® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.


---

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

2-24-2026 21:34 - US/CA



**Technical Information**

All product dimensions are nominal.

Basin configuration: Single Bowl  
Min. base cabinet width: 36" (914 mm)

Bowl area (Only): Length: 29-1/4" (743 mm)  
Width: 15" (381 mm)  
Bowl depth: 9-1/4" (235 mm)  
Water depth: 9" (229 mm)

Number of deck holes: 4

Faucet hole(s): 1-7/16" (37 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1032929-7, not required, not included

**Notes**

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.