





### Features


- Brass Construction
- Deck-mount installation
- KOHLER finishes resist corrosion and tarnishing.
- Lever handle
- Includes leak-free ceramic disc valve
- Includes flexible G1/2 supply hoses for easy installation
- Includes handshower
- Includes hose
- Includes diverter



### Available Colors/Finishes

*Color tiles intended for reference only.*

| Color  | Code | Description |
|--|------|-------------|
|    | CP   |             |
|    | AF   |             |
|  | TT   |             |



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 8 gal/min (30.3 l/min)

Pressure: 45 psi (3.1 bar)

#### Handshower:

Rated maximum flow: 2.37 gal/min (9 l/min)

### Notes

Install this product according to the installation instructions.