



Numi® Comfort Height®

Intelligent elongated dual-flush chair height toilet

K-3901-NPR

Features

- Compact, streamlined one-piece intelligent toilet with integrated personal cleansing.
- Elongated bowl offers added room and comfort.
- Comfort Height® feature offers chair-height seating that makes sitting down and standing up easier for most adults.
- Motion-activated, hands-free opening/closing of seat and cover.
- Advanced bidet functionality with self-cleaning wand, precision air dryer, and deodorizing filter all in one.
- Adjustable heated seat and foot warmer.
- Ambient lighting with eight colors and three programming options.
- Power-save mode monitors usage and adjusts heated seat settings to save energy.
- Emergency flush supports up to 100 flushes during power outage.
- Syncs with devices enabled with BLUETOOTH® wireless technology including smartphones, MP3 players, tablets, and laptops located up to 33 feet away.*

Technology

- Touch-screen remote control with magnetic wall-mount docking/charging station.
- User presets for up to six people to recall individual saved preferences.
- Remote is adjustable to 12 different languages.
- Remote includes lithium polymer rechargeable battery.
- Preferred remote for residential settings.
- Dual-flush technology allows you to choose between a full or partial flush.

Installation

- A drain line grade of ¼ per foot minimum is required.
- Standard 12" (305 mm) rough-in.
- Requires a supply stop with ½" OD compression male outlet thread.

Recommended Products/Accessories

K-23726 Drain treatment

Included Components

Additional Components:

K-7420 Premium Remote Control
Block mounting kit
Inlet hose kit
Supply line



Codes/Standards

ASME A112.19.14
ASME A112.4.2/CSA B45.16
ASME A112.19.2/CSA B45.1
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
UL 1951
CSA C22.2 No. 14
CSA C22.2 No. 68

KOHLER® Intelligent Toilet and C3® Cleansing Seat Three-Year Limited Warranty

See website for detailed warranty information.

The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license. Other trademarks and trade names are those of their respective owners.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	HB1	Honed Black


1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com.

5-16-2021 06:30 - US/CA

THE BOLD LOOK
OF **KOHLER®**



Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

120 V, 15 A, 60 Hz

Technical Information

All product dimensions are nominal.

Toilet type:	One-piece, Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Trap passageway:	2-7/8" (73 mm)
Water Consumption	
Full:	1.28 gpf (4.8 lpf)
Reduced:	0.6 gpf (2.3 lpf)
Water surface size:	10" x 8-1/4" (254 mm x 210 mm)
Rim to water surface:	5-1/2" (140 mm)
Rough-in:	12" (305 mm)

Fixture Supply Requirements

Min static pressure:	30 psi (206.8 kPa)
Max static pressure:	80 psi (551.6 kPa)

Notes

Install this product according to the installation instructions.

IMPORTANT! Use the supply hoses provided with the fixture. Do not reuse the previously installed hoses.

Installation of a water hammer arrestor is recommended.

Install the docking station cord, when premium remote control is included, before installing the finished wall.

The supplied water inlet hose requires a supply stop with a 1/2" OD compression male outlet thread.

If local codes require the toilet be bolted to the flange, order flange installation kit for required hardware and instructions.

Can be installed with water and electrical supplies attached to the back wall or through the floor. See roughing-in illustration for details.

Adjust the through-the-floor installation as required to meet all local codes.