

Features

- Elongated bowl offers added room and comfort
- Skirted trapway simplifies cleaning
- 2" (51 mm) glazed trapway
- Combines with the 402098 or 402098-RA tank to create a complete 402095 or 402095-RA Brella two-piece toilet
- Patented ReadyLock® installation system, a simple solution for skirted toilets, saves time, hassle, and eliminates the need to drill into the floor for standard 12" (305 mm) rough-in

Installation

- Standard 12" (305 mm) rough-in
- Seat and supply line sold separately
- Three-bolt quick-connect installation


Recommended Products/Accessories

K-26801 Impro® ReadyLatch® Quiet-Close™ elongated toilet seat

Codes/Standards

ASME A112.19.2/CSA B45.1

STERLING® Toilet Limited Warranty
See website for detailed warranty information.



DISCONTINUED This product has been discontinued.

DISCONTINUED This product has been discontinued.

No image available.
This product is a component and not intended to be a standalone installation.

DISCONTINUED This product has been discontinued.

Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Trap passageway:	2" (51 mm)
Water surface size:	5-1/16" x 4-9/16" (129 mm x 115 mm)
Rim to water surface:	8-9/16" (217 mm)
Rough-in:	12" (305 mm)
Seat-mounting holes:	5-1/2" (140 mm)

Notes

Install this product according to the installation instructions.

A 1" (25 mm) gap between the toilet and the wall is required.