



Windham™

Two-piece elongated toilet, 1.28 gpf
402321-WRA

Features

- Two-piece design
- Elongated bowl offers added room and comfort
- Standard height
- 1.28 gpf (4.8 lpf)
- Color-matched right-hand white trip lever included
- 2-1/8" (54 mm) fully glazed trapway
- Combination consists of toilet bowl and tank
- Pro Force® Plus flushing technology delivers greater flushing power than previous Pro Force® models

Installation

- Three-bolt quick-connect installation
- Standard 12" (305 mm) rough-in
- Seat and supply line sold separately

Recommended Products/Accessories

K-4774 Brevia™ Quick-Release™ elongated toilet seat

Included Components

402362-WRA Toilet tank, 1.28 gpf
403217 Elongated toilet bowl



Codes/Standards

ASME A112.19.2/CSA B45.1
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)

STERLING® Toilet Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Flush type:	ProForce Plus
Trap passageway:	2-1/8" (54 mm)
Rim to water surface:	6-9/16" (167 mm)
Rough-in:	12" (305 mm)

Fixture Supply Requirements

Min static pressure:	20 psi (137.9 kPa)
Max static pressure:	80 psi (551.6 kPa)
Min flowing pressure:	15 psi (103.4 kPa)
Min flow rate:	1 gpm (3.8 lpm)

Notes

Install this product according to the installation instructions.

Product dimensions are nominal and may vary per ASME A112.19.2 tolerances.