




Windham™
Toilet tank, 1.6 gpf
402363-WTL

Features

- 1.6 gpf (6.0 lpf)
- Color-matched left-hand white trip lever included
- Combines with 403017, 403217, 403317 bowl to make a complete 402323-WTL, 402324-WTL, 402325-WTL toilet

Required Products/Accessories

- 403017 Round-front toilet bowl
- 403217 Elongated toilet bowl
- 403317 Elongated chair height toilet bowl



Codes/Standards

ASME A112.19.2/CSA B45.1

STERLING® Toilet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



Windham™
Toilet tank, 1.6 gpf
402363-WTL

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type: Bowl-mount

Flush type: ProForce Plus

Fixture Supply Requirements

Min static pressure: 20 psi (137.9 kPa)

Max static pressure: 80 psi (551.6 kPa)

Min flowing pressure: 15 psi (103.4 kPa)

Min flow rate: 1 gpm (3.8 lpm)

Notes

Install this product according to the installation instructions.

Product dimensions are nominal and may vary per ASME A112.19.2 tolerances.