



Stinson®

Elongated chair height toilet bowl

403316

Features

- Elongated bowl offers added room and comfort
- Comfort Height® feature offers chair-height seating that makes sitting down and standing up easier for most adults
- 2" (51 mm) fully glazed trapway
- Floor Saver® footprint helps cover the old footprint left by many standard two-piece toilets
- Combines with a 404558, or 404558-RA tank to create a complete 402396 or 402396-RA two-piece toilet

Installation

- Standard 12" (305 mm) rough-in
- Three-bolt quick-connect installation
- Seat sold separately

Recommended Products/Accessories

K-23726 Drain treatment



Codes/Standards

ASME A112.19.2/CSA B45.1

STERLING® Toilet Limited Warranty

See website for detailed warranty information.



Stinson®
Elongated chair height toilet bowl
403316

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Flush type:	ProForce Plus
Trap passageway:	2" (51 mm)
Rough-in:	12" (305 mm)

Notes

Install this product according to the installation instructions.

Product dimensions are nominal and may vary per ASME A112.19.2 tolerances.