

### Features


- Elongated bowl offers added room and comfort
- Comfort Height® feature offers chair-height seating that makes sitting down and standing up easier for most adults
- 2-1/8" (54 mm) fully glazed trapway
- Combines with 402362, 402362-RA, 402363, 402363-RA tanks to make a complete 402322, 402322-RA, 402325, 402325-RA toilet
- Pro Force® Plus flushing technology delivers greater flushing power than previous Pro Force® models

### Installation

- Three-bolt quick-connect installation
- Standard 12" (305 mm) rough-in
- Seat and supply line sold separately

### Recommended Products/Accessories

402362 Toilet tank  
402362-RA Toilet tank  
402363 Toilet tank  
402363-RA Toilet tank  
K-23726 Drain treatment



### Codes/Standards

ASME A112.19.2/CSA B45.1


### STERLING® Toilet Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



**Windham™**  
Elongated chair height toilet bowl  
**403317**

No image available.  
This product is a component and not intended to be a standalone installation.

**Technical Information**

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Flush type:	ProForce Plus
Trap passageway:	2-1/8" (54 mm)
Water surface size:	9-1/2" x 7" (241 mm x 178 mm)
Rim to water surface:	6-1/2" (165 mm)
Rough-in:	12" (305 mm)
Seat-mounting holes:	5-1/2" (140 mm)

**Notes**

Install this product according to the installation instructions.

Product dimensions are nominal and may vary per ASME A112.19.2 tolerances.