



Garwind™

The Complete Solution® elongated toilet

404715

Features

- Two-piece toilet.
- Elongated bowl offers added room and comfort
- Comfort Height® seating makes sitting down and standing up easier for most adults.
- 1.28 gallons per flush (gpf).
- Standard left-hand chrome trip lever included.
- 2" fully glazed trapway.
- Complete Solution® toilets provide everything you need in one box, including bowl, tank, seat, wax ring and floor hardware.
- Pro Force® Plus flushing technology delivers greater flushing power than previous Pro Force® models
- Three-bolt quick-connect installation system.

Installation

- Standard 12" rough-in.
- Supply line not included.

Recommended Products/Accessories

K-5588 Purefresh® Deodorizing elongated toilet seat
K-5420 Low-Profile Bolt Caps



ADA **CSA B651** **OBC**

Codes/Standards

ASME A112.19.2/CSA B45.1
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1
CSA B651
OBC

STERLING® Toilet Limited Warranty

See website for detailed warranty information.

DISCONTINUED This product has been discontinued.

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

6-29-2026 05:00 - US/CA



Toilet type: Floor-mount

Waste Outlet: Floor

Bowl shape: ☒ Elongated

Flush type: ProForce Plus

Trap passageway: 2" (51 mm)

Rough-in: 12" (305 mm)

Fixture Supply Requirements

Min static pressure: 15 psi (103.4 kPa)

Max static pressure: 80 psi (551.6 kPa)

Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

Plumbing codes may require elongated toilets and elongated, open-front seats in public bathrooms.

Accessibility standards may require controls to be located on the open side of the toilet.