



Stinson®

20" rectangle undermount bathroom sink
442007-U

Features

- Center drain and overflow
- Modern rectangular shape
- No faucet holes; requires wall- or counter-mount faucet

Material

- Crafted of Grade A vitreous china to provide a durable, nonporous product with a glossy finish

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23725 Cast iron cleaner

Included Components

- 1193643 Basin clamps



ADA

Codes/Standards

- ASME A112.19.2/CSA B45.1
- ADA
- ICC/ANSI A117.1

STERLING® Vitreous China Bathroom Sinks Five-Year Limited Warranty



See website for detailed warranty information.

Available Colors/Finishes



Color tiles intended for reference only.

Color Code Description

	0	White
--	---	-------



Recommended ADA Installation



Technical Information

All product dimensions are nominal.

- Basin configuration: Single Bowl
- Bowl area (Only): Length: 18-3/16" (462 mm)
Width: 11-7/8" (302 mm)
Water depth: 5" (127 mm)
- With overflow: Yes
- Drain hole: 1-11/16" (43 mm)

Notes

- Install this product according to the installation instructions.
- Measure your actual product for roughing-in details.
- Product dimensions are nominal and may vary per ASME A112.19.2 tolerances.
- ADA compliant when installed to the specific requirements of these regulations.