

BEFORE YOU BEGIN

开始之前

• Congratulation on your purchase of this high quality Bathroom Accessory. Before proceeding with the installation, please carefully read this installation instruction in order to ensure proper care and assembly of this accessory.

• 首先恭喜您购买到了高档的卫浴产品，为了使您正确保护和组装产品，在您安装之前请详细阅读此说明书。

• Please keep this installation instruction for future reference.

• 请保留此说明书以备参考。



Prior to drilling into walls, check there are no hidden electrical wires, cables or water supply pipes with the aid of an electronic detector. If you use power tools do not forget:

1. Wear eye protection.
2. Unplug equipment after use.



警示：在钻孔之前，请借助电子探测仪确认墙内是否有电源线，通讯光缆或者水管之类的东西。如果使用电钻的话请勿忘记以下两点：

1. 请戴上防护镜。
2. 用完设备后关掉电源。


ROUGHING-IN

尺寸图

Reference Value
参考值


UNIT : mm
单位：毫米

K-15478T



科勒(中国)投资有限公司
上海市闸北区江场三路158号 邮编：200436

K-15479T/K-45101T



科勒公司保留随时变更图中标示尺寸的权利，无需另行通知。

Kohler reserves the right to change marked dimensions without prior notice.

PREPARE THE SITE

安装准备

NOTE:

1. For the sake of your safety, please turn off the electricity before installation, dismantling or cleaning.
2. The installation is suggested to be executed by certified electrician, and the ground wires should be properly connected.

注意:

1. 为了你的安全，请在安装与拆卸或清洁此产品前，需先关掉电源。
2. 建议由有资格的电工安装并确保连接好地线。

INSTALLATION


安装步骤

Note: Please make sure power is shut off before installation.

注意：安装之前请确认已经关闭电源。


1. Put the mounting plate at the desired place for installation. Drill 7 installation holes with a 6mm drill.
2. Insert the wall anchors into the drilled holes on the wall.
3. Pull the wire through the thread hole on the mounting plate.
4. Fix the mounting plate on the wall with screws and then tighten the wall anchors.

1. 在希望安装的位置放置背板，用6mm钻头钻好7个安装孔；
2. 将入墙胶粒按安装孔位塞入需要安装的墙壁上；
3. 将电源线穿过背板的过线孔；
4. 用安装螺钉将背板锁在墙壁上，安装螺钉锁紧入墙用胶粒。




5. Connect the plug with the socket.
6. Fix the fluorescent lamp to the spring slice.

5. 将灯管插头与灯管插座连接；
6. 将荧光灯管安装在弹片上。




7. Drill through the pre-prepared hole on the lampshade.
8. Pull the waterproof wire clip through the pre-prepared hole on the lampshade. Tighten the nut with the waterproof wire clip.

7. 将灯罩上的预留孔打通；
8. 将防水线扣穿过灯罩上的预留孔，用防水线扣将螺母锁紧。




9. Pull the power line through the waterproof wire clip on the lampshade and bind it on the fixture.
10. Bind the waterproof plug wire to the fixture.

9. 将电源线穿过灯罩上的防水线扣锁在接线柱上；
10. 将灯罩上的防水插头线锁在接线柱上。



Fixture 接线柱	Waterproof Plug Wire 防水插头线
	Hot Wires 地线
N	Neutral Wires 零线
L	Ground Wires 火线




11. Fix the lampshade on the mounting plate with screws.

11. 用螺丝将灯罩固定在背板上。


Note: The seal ring must be embedded into the lampshade.

注意：密封圈一定要嵌在灯罩上。




12. Pull the screw through the bracket and the mounting hole. Tighten the wall anchors.

12. 将安装螺钉1穿过固定架及安装孔锁在墙壁上，锁紧入墙胶粒。



13. Drill $\varnothing 6\text{mm}$ holes according to lamp location and mirror size, then insert anchor.


13. 根据灯的位置及镜子大小钻孔并塞入入墙胶粒。



SKU	L1	L2
15478T	200	300
15479T	140	50
45101T	230	50

14. Fix the supporting block onto wall with screws. Tighten the wall anchors.

14. 用安装螺钉2将支撑垫锁在墙壁上，锁紧入墙胶粒。



15. Connect the waterproof gasket with the socket and then tighten the socket with the plug.

15. 将防水插座加上防水垫片与防水插头扭紧；

16. Hang the hook to the bracket.

16. 将挂钩挂在固定架上；

17. Turn on power to check whether the lamp and the defogger are functioning.

17. 打开电源开关测试灯和防雾膜是否正常工作。

