

Features

- Brass construction
- Optimized sprayface and large nozzles with Katalyst® Air-induction for improved water coverage
- Precise thermostatic valve with over-ridable temperature stop for added safety
- Durable KOHLER finishes resist corrosion and tarnishing
- Adjustable inlet fittings with 15mm tolerance
- Hose connection for flexible installation
- Includes 8" round comfort Katalyst Air Rainhead
- Includes 110 mm Renew Organic 3-function handshower

Codes/Standards Applicable

Specified model meets or exceeds the following:

- EN 1111-1998
- QB 2806-2006
- GB/T 23447-2009

Installation Notes

Install this product according to the installation guide.



THERMOSTATIC DUAL SHOWER COLUMN 45352T-C9



Specified Model

Model	Description	Color/Finished		
45352T-C9	JULY Thermostatic Dual Shower Column-Angular	<input type="checkbox"/> Polished Chrome (CP)	<input type="checkbox"/> French Gold (AF)	<input type="checkbox"/> Brushed Nickel (BN)


For a full range of color finishes in your market please contact your local Kohler representative.



- Note: 1. Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)
 2. Flow rates shown with supplied flow regulators installed.

Dimensions are approximate.

Unit: mm



Product Diagram