

Features

- Vitreous China
- With Overflow
- Above counter

Recommended Accessories

- Bottle Trap (75823IN)
- Grid Drain with overflow hole (45432IN)







Material	Description
99858IN-4-CP	BEITOU SINGLE CONTROL TALL LAV FAUCET
97347IN-4-CP	AVID SC TALL LAV FAUCET WITH DRAIN
73053IN-4-CP	COMPOSED SC JOYSTICK TALL LAV FCT. W/D
73159IN-7-CP	COMPOSED SC SIDE MOUNT TALL LAV FCT. W/D
10861IN-4ND-CP	SINGULIER SINGLE LEVER TALL LAV FAUCET
72337IN-4ND-CP	ALEO+ TALL LAV FAUCET W/O DRAIN
72298IN-4-CP	ALEO TALL LAV FAUCET W/ DRAIN
37334IN-4-CP	STRAYT TALL PILLAR TAP
11546IN-4-CP	SINGULIER TALL PILLAR LAVATORY FAUCET
20071IN-4-CP	ALEO+ PILLAR TAP, TALL
20070IN-4-CP	ALEO PILLAR TAP, TALL


KOHLER® Ten-Year Limited Warranty

See website for detailed warranty information.

Available *Color/ Finishes

Color tiles intended for reference only

Color	Code	Description
	0	White
	HG1	Honed Thunder Grey
	HP1	Honed Peacock
	HT1	Honed Truffle



Notes

Install this product according to the installation instructions.

Product has an overflow channel.

*Spout must be 3.9" (99mm) long (min) for adequate clearance into the bathroom sink.

NOTICE: Counter cutting should be done using the cut-out template provided with the product. Kohler is not responsible for any cutout errors.

Technical Information

All Product Dimensions are nominal

Lavatory configuration	Single
Installation	Above Counter
Bowl area	Length: 22 5/8" (575 mm) Width: 16 1/8" (410 mm) Height: 6 7/8" (174 mm) Depth: 4 15/16" (125 mm)
Drain hole	Ø41.65 - Ø46.5 mm
Template	1335595-K7