

### Features

- Brass construction
- Optimized sprayface and large nozzles with Katalyst® Air-induction for improved water coverage
- Leak-free ceramic disc valve with lifetime warranty
- Durable KOHLER finishes resist corrosion and tarnishing
- 165mm spout reach
- Adjustable inlet fittings with 15mm tolerance
- Hose connection for flexible installation
- Includes 8" round comfort Katalyst Air Rainhead
- Includes 110 mm Awaken Geometric 3-function handshower

### Codes/Standards Applicable

Specified model meets or exceeds the following:

- EN 817-2008
- GB/T 23447-2009



### Installation Notes

Install this product according to the installation guide.

### Specified Model

Model	Description	Color/Finished		
5428T-C4	JULY Dual Shower Column-Angular	<input type="checkbox"/> Polished Chrome (CP)	<input type="checkbox"/> French Gold (AF)	<input type="checkbox"/> Brushed Nickel (BN)


For a full range of color finishes in your market please contact your local Kohler representative.



- Note: 1. Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)  
2. Flow rates shown with supplied flow regulators installed.

Dimensions are approximate.

Unit: mm



### Product Diagram