



OC-S-63

63-1/4" x 39-3/8" Vikrell® roll-in shower with Aging in Place backerboards, center drain

62070106



Features

- 1/2" (12.7 mm) threshold
- Durable swirl-gloss finish
- Three-piece tongue-and-groove walls with snap-together installation
- Aging in Place backerboards

Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

Installation

- Alcove
- Center drain
- Caulk required for proper installation

Recommended Products/Accessories

K-23726 Drain treatment

Included Components

62055106 39-3/8" Vikrell® shower end wall set with Aging in Place backerboards
62061100 63-1/2" x 39-3/8" Vikrell® roll-in shower base, center drain, center drain
62062106 63-1/4" Vikrell® shower back wall with Aging in Place backerboards



Codes/Standards

CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Drain location: Center

Notes

Install this product according to the installation instructions.

Drain cutout in subfloor to be 10-1/2" (267 mm) per rough-in illustration as shown to allow the backside of the drain to sit below the subfloor surface.

Backerboards and fasteners protrude beyond the back wall 1-1/2" (38 mm). If installing this product against wall board, 1-1/2" (38 mm) furring strips installed over the wall board are recommended. The stud pocket depth of 40-5/8" (1032 mm) will need to be increased by the combined thickness of the wall board and furring strips.

Studs should be positioned as shown.

Attach grab bars at the specified backerboard locations only.