



* Color code must be specified when ordering.
 * 订购时请说明颜色编号。

P/N 零件号	DESCRIPTION 描述	COLOR 颜色		
★ 1343895-R*	Door Glass, RH, New Purist, 10mm 门玻璃 (右开)	FM, IC		
★ 1343896-R*	Panel Glass, RH, New Purist, 10mm 固定玻璃 (右开)			
★ 1343895-L*	Door Glass, LH, New Purist, 10mm 门玻璃 (左开)			
★ 1343896-L*	Panel Glass, LH, New Purist, 10mm 固定玻璃 (左开)			
★ 1343941*	Panel Glass With Big Shelf, New Purist, 10mm 七件套固定玻璃			
★ 1343942*	Panel Glass With Small Shelf, New Purist, 10mm 五件套固定玻璃			
★ 1343898*	Wall Channel Clamp, New Purist 新飘瑞诗上墙材	2BL, SHP		
★ 1343906*	Wall Jamb Clamp, New Purist 新飘瑞诗夹材	2BL, SHP		
★ 1343908*	Wall Jamb Clamp Cap, New Purist 新飘瑞诗夹材装饰材	2BL, SHP		
★ 1343916*	Side Frame, New Purist 新飘瑞诗边立柱	2BL, SHP		
★ 1341594-R*	Bottom Frame, RH, New Purist 新飘瑞诗底横梁 (右开)	2BL, SHP		
★ 1341594-L*	Bottom Frame, LH, New Purist 新飘瑞诗底横梁 (左开)	2BL, SHP		
1341489*	Cover Cap, New Purist 新飘瑞诗铝材装饰盖	2BL, SHP		
★ 1331771*	Trolley Flat Tube 10X30 不锈钢扁管	2BL, S, RGD, AF, BN, BV		
1325088-R*	Hinge Assy, Up, RH, New Purist 新飘瑞诗上铰链组件 (右开)	2BL, S, RGD, AF, BN, BV		
1325149-R*	Hinge Assy, Bottom, RH, New Purist 新飘瑞诗下铰链组件 (右开)	2BL, S, RGD, AF, BN, BV		
1325088-L*	Hinge Assy, Up, LH, New Purist 新飘瑞诗上铰链组件 (左开)	2BL, S, RGD, AF, BN, BV		
1325149-L*	Hinge Assy, Bottom, LH, New Purist 新飘瑞诗下铰链组件 (左开)	2BL, S, RGD, AF, BN, BV		
1331780*	Panel Glass Trolley Body Assy, New Purist 固坡拉杆夹具座组件	2BL, S, RGD, AF, BN, BV		
1331782*	Trolley Wall Body Assy, New Purist 拉杆上墙座组件	2BL, S, RGD, AF, BN, BV		
1111937*	Screw Cover Cap M6 CSK Grey 螺丝盖帽	2BL, CP, RGD, AF, BN, BV		
★ 1272963*	Composed Handle Assy, 450mm, Double 对装柏诗拉手 450mm	2BL, S, RGD, AF, BN, BV		
★▲ 1343935	New Purist Pivot Seal Strip Package Kit, 10mm 新飘瑞诗开门密封配件包	1343931	Insert Magnetic Seal, 10mm, Skyline 铝材磁条	
		1343932	Magnetic Seal, 180°, 10mm 180度门吸磁条	
		1343940	Magnetic Seal, Inward Opening, 10mm 内开磁条	
		1343929	Bottom Seal For Purist DR Glass Profile 门底胶条	
		1343930	Side Seal, 10mm, Profile, Hinged Door 侧边胶条	
		1343952	Side Seal, Inner Open, New Purist, 10mm 内开门侧边胶条	
		1343933	Glass Gripping Seal, Profile, 10mm 固坡压紧胶条	
		1343934	Inserted Seal For Bottom Frame 底横梁嵌入胶条	
★▲ 1343922	New Purist Pivot SP Package Kit 新飘瑞诗开门维修配件包	1157883	Insert Seal, 8mm 单边胶条	
		1272936	Connector Block 塑胶压块	
		1210861	Screw ST3.5X6 非尖头螺丝 (锁塑胶压块用)	
		1283425	Screw ST3.9X12 十字沉头自攻螺丝 ST3.9X12 (锁端盖用)	
		1343936	Screw M4X8 十字沉头机制螺钉 M4X8	
		1343947	Screw M5X8 平头顶丝 M5X8	
		1150121	Screw, GB/T 845 ST3.5X40 盘头十字自攻螺钉 ST3.5X40	
		1057064	Wall Anchor 膨胀套 (入墙胶粒)	
		1157853	Screw Key 2.5mm 2.5mm 内六角扳手	
		1095457	Screw Key 3mm 3mm 内六角扳手	
		1078917	Screw Key 4mm 4mm 内六角扳手	
		1178609	Screw Key 5mm 5mm 内六角扳手	

Note: Components marked in ▲ can only be ordered in whole pack. When ordering components marked in ★, customers need provide measurement form and corresponding product SKU.

注意: 带▲标注零件仅可整包订购, 带★标注零件订购时需附加测量单和产品 SKU 号。

Glass options: L3, L4, L5, L8, L9, C, CI, EL, MZ, GB
玻璃花纹可供选择 L3, L4, L5, L8, L9, C, CI, EL, MZ, GB

FM-It is for filmed glass. The following decorative patterns can be chosen (refer to the table below) together with FM glass.
IC-It is for laminated glass with easy clean coating. The following decorative patterns cannot be chosen together with IC glass.

FM- 此号码为防爆膜玻璃, 配备 FM 时, 可以选择以下指定花纹代码 (参考下表)。
IC- 此号码为夹层 + 超净玻璃, 配备 IC 时, 以下代码不能再选择。

Refer to the table below for glass options
玻璃选项参考下表

P/N	Description
1291888-L1	蕾丝花纹, L1
1291888-L3	思绪花纹, L3
1291888-L4	梅玛花纹, L4
1291888-L5	晨雾花纹, L5
1291888-L8	繁星花纹, L8
1291888-L9	丝雨花纹, L9
1291888-MZ	镜面玻璃, MZ
1291888-CI	镜面繁星花纹, CI
1291888-EL	镜面银河花纹, EL
1291888-GB	金色夏宫花纹, GB
1291888-C	超净玻璃, C