



\* Color code must be specified when ordering.  
 \* 订购时请说明颜色编号

P/N 零件号	DESCRIPTION 描述		COLOR 颜色
★ 1341921	Door Glass, Components, 10mm 门玻璃 10mm		FM, IC
★ 1341922	Panel Glass, Components, 10mm 固定玻璃 10mm		
★ 1341976-*	Panel Glass with Big Shelf, Components, 10mm 七件套固定玻璃 10mm		
★ 1341977-*	Panel Glass with Small Shelf, Components, 10mm 五件套固定玻璃 10mm		
★ 1341511-R-*	Wall Jamb-R, Insert Glass 夹固玻璃立柱-R		
★ 1341511-L-*	Wall Jamb-L, Insert Glass 夹固玻璃立柱-L		2BL, S
★ 1341512-*	Jamb, Inner 内侧墙立柱		2BL, S
★ 1341513-R-*	Jamb-R, Lateral 外侧墙立柱-R		2BL, S
★ 1341513-L-*	Jamb-L, Lateral 外侧墙立柱-L		2BL, S
★ 1341514-R-*	Jamb-R, Door Bottom 一固一活下横梁-R(通用L型)		2BL, S
★ 1341514-L-*	Jamb-L, Door Bottom 一固一活下横梁-L(通用L型)		2BL, S
★ 1341516-*	Cover, Wall Jamb 墙立柱装饰盖		2BL, S
1341517-*	End Cover, Wall Jamb 外侧立柱端盖		2BL, S
1341518-*	End Cover, Solid Glass Wall Jamb 夹固玻璃立柱端盖		2BL, S
1341527-*	Cover, Briquetting Decorative 下导轨固定件端盖		2BL, S
★ 1341931-*	SS Tube, 10*30, Components 10*30 不锈钢扁管		2BL, S, RGD, AF, BN
1331782-*	Trolley Wall Body Assy 拉杆上墙座组件		2BL, S, RGD, AF, BN
1341605-*	Panel Glass Trolley Body Assy 固玻拉杆夹紧座组件		2BL, S, RGD, AF, BN
1341483	Soft Close Hinge, Up 艺廷系列闭门铰链		
1341484	Soft Close Hinge, Down 艺廷系列阻尼铰链		
1341969-*	Cover Assy, Hinge 缓冲铰链外盖组件		2BL, S, RGD, AF, BN
1111937-*	Screw Cover Cap M6 CSK Grey 螺丝盖帽		2BL, CP, RGD, AF, BN
1341838-*	Components Handle, Double Handle, L=450mm 艺廷拉手, 对装, L=450mm		2BL, S, RGD, AF, BN
★▲ 1341974	Components Pivot Seal Strip Package Kit, 10mm 艺廷开门密封配件包 10mm	1341685	Bubble Seal 泡泡胶条
		1341520	Magnetic Seal 型材内侧磁条
		1343926	Magnetic Seal 磁条 (The 1D1P shall be purchased together with 1341520 as a pair. The rest shall be purchased in pair.) (一固一活与1341520 配对购买, 其余成对单买)
		1341932-R	Seal Assy, Moving Glass Bottom, RH 回水槽组件 (右)
		1341932-L	Seal Assy, Moving Glass Bottom, LH 回水槽组件 (左)
		1341526	Seal, Bottom Door 固玻底下装饰胶条
		1157883	Insert Seal 单边胶条
▲ 1341975	Components Pivot SP Package Kit 艺廷开门维修配件包	1273872	Screw M4X6 (For locking end cover) 半圆头内六角机制螺丝 M4X6 (锁端盖用)
		1341524	Briquetting 下导轨固定件
		1341528	Screw, Adjust 调节螺杆
		1291052	Install Sleeve 安装套管
		1341557	Screw M4*10 十字沉头机制螺钉 M4*10
		1150121	Screw, GB/T 845 ST3.5X40 盘头十字自攻螺钉 ST3.5X40
		1057064	Wall Anchor 膨胀套 (入墙胶粒)
		1157853	Screw Key 2.5mm 内六角扳手 2.5mm
		1095457	Screw Key 3mm 内六角扳手 3mm
1078917	Screw Key 4mm 内六角扳手 4mm		

Note: Components marked in ▲ can only be ordered in whole pack. When ordering components marked in ★, customers need provide measurement form and corresponding product SKU.

注意: 带▲标注零件仅可整包订购, 带★标注零件订购时需附加测量单和产品SKU号。

Glass options: C, L3, L4, L5, L8, L9, CI, EL, MZ, GB, GG, GA, GR, TA, SW  
 玻璃花纹可供选择: C, L3, L4, L5, L8, L9, CI, EL, MZ, GB, GG, GA, GR, TA, SW

FM-It is for filmed glass. Please refer to the table for FM glass.  
 FM-此号码为防爆膜玻璃, 配备FM时, 只能按照FM玻璃选项参考表指定花纹代码。

IC-It is for laminated glass with easy clean coating. Please refer to the table for IC glass.  
 IC-此号码为夹层+超净玻璃, 配备IC时, 只能按照IC玻璃选项参考表指定花纹代码。

Table for FMSW glass  
 FMSW 玻璃选项参考表

P/N 零件号	DESCRIPTION 描述
1291888-L3	思绪花纹, L3
1291888-L4	梅玛花纹, L4
1291888-L5	晨雾花纹, L5
1291888-L8	繁星花纹, L8
1291888-L9	丝雨花纹, L9
1291888-MZ	镜面玻璃, MZ
1291888-CI	镜面繁星花纹, CI
1291888-EL	镜面银河花纹, EL
1291888-GB	金色夏宫花纹, GB
1291888-C	超净玻璃, C
1291888-GR-NA	墨韵灰, GR
1291888-TA-NA	琥珀棕, TA
1291888-BSZ-NA	金色臻彩绘印图案小, BSZ
1291888-BMZ-NA	金色臻彩绘印图案中, BMZ
1291888-BLZ-NA	金色臻彩绘印图案大, BLZ
1291888-GSZ-NA	灰色臻彩绘印图案小, GSZ
1291888-GMZ-NA	灰色臻彩绘印图案中, GMZ
1291888-GLZ-NA	灰色臻彩绘印图案大, GLZ

Table for IC glass  
 IC玻璃选项参考表

P/N 零件号	DESCRIPTION 描述
1291888-GG-NA	烟云灰, GG
1291888-GA-NA	旭日金, GA