



* Color code must be specified when ordering.
* 订购时请说明颜色编号。

P/N 零件号	DESCRIPTION 描述	COLOR 颜色		
★1341923	Door Glass, Components Hinge 10mm 门玻璃 10mm	FM, IC		
★1341924	Panel Glass, Components Hinge 10mm 固定玻璃 10mm			
★1341925	Panel Glass, Magnetic Seal, Components Hinge 磁条侧固定玻璃			
★1341983-*	Panel Glass with Big Shelf, Components Hinge 10mm 七件套固定玻璃 10mm			
★1341984-*	Panel Glass with Small Shelf, Components Hinge 10mm 五件套固定玻璃 10mm			
★1361151-*	SS Tube, 10*15, Components Screen, 1D2P 两固一活不锈钢下挡水条 10*15	2BL, S, RGD, AF, BN		
1361149-*	Cover 固定件装饰盖	2BL, S, RGD, AF, BN		
1341818-*	Side Wall Clip Assy 艺廷单头墙夹组件	2BL, S, RGD, AF, BN		
★1341931-*	SS Tube, 10*30, Components 10*30 不锈钢扁管	2BL, S, RGD, AF, BN		
1331782-*	Trolley Wall Body Assy 拉杆上墙座组件	2BL, S, RGD, AF, BN		
1341605-*	Panel Glass Trolley Body Assy 固玻拉杆夹紧座组件	2BL, S, RGD, AF, BN		
1341483	Soft Close Hinge, Up 艺廷系列闭门铰链			
1341484	Soft Close Hinge, Down 艺廷系列阻尼铰链			
1341969-*	Cover Assy, Hinge 缓冲铰链外盖组件	2BL, S, RGD, AF, BN		
1111937-*	Screw Cover Cap M6 CSK Grey 螺丝盖帽	2BL, CP, RGD, AF, BN		
1341838-*	Components Handle, Double Handle, L=450mm 艺廷拉手, 对装, L=450mm	2BL, S, RGD, AF, BN		
★▲1341987	Components Hinge Pivot Seal Strip Package Kit 10mm 艺廷开门密封配件包 10mm	1341685	Bubble Seal 泡泡胶条	
		1343926	Magnetic Seal 磁条	
		1341932-R	Seal Assy, Moving Glass Bottom, RH 回水槽组件(右)	
		1341932-L	Seal Assy, Moving Glass Bottom, LH 回水槽组件(左)	
▲1341988	Components Hinge Pivot SP Package Kit 艺廷开门维修配件包	1269842	Screw M5*10 不锈钢十字平头机制 M5*10	
		1361147	Gasket 胶垫	
		1361148	Fixed Piece 固定件	
		1269841	Screw M5*22 不锈钢十字平头机制 M5*22	
		1341989	Screw, GB/T 845 ST3.5x40 不锈钢沉头自攻(高低牙) ST3.5x40	
		1057064	Wall Anchor 膨胀套(入墙胶粒)	
		1157853	Screw Key 2.5mm 内六角扳手 2.5mm	
		1095457	Screw Key 3mm 内六角扳手 3mm	
		1078917	Screw Key 4mm 内六角扳手 4mm	

Note: Components marked in ▲ can only be ordered in whole pack. When ordering components marked in ★, customers need provide measurement form and corresponding product SKU.

注意：带▲标注零件仅可整包订购，带★标注零件订购时需附加测量单和产品SKU号。

Glass options: C, L3, L4, L5, L8, L9, CI, EL, MZ, GB, GG, GA, GR, TA, SW
 玻璃花纹可供选择：C, L3, L4, L5, L8, L9, CI, EL, MZ, GB, GG, GA, GR, TA, SW

FM-It is for filmed glass. Please refer to the table for FM glass.
 FM-此号码为防爆膜玻璃，配备FM时，只能按照FM玻璃选项参考表指定花纹代码。

IC-It is for laminated glass with easy clean coating. Please refer to the table for IC glass.
 IC-此号码为夹层+超净玻璃，配备IC时，只能按照IC玻璃选项参考表指定花纹代码。

Table for FMSW glass
 FMSW 玻璃选项参考表

P/N 零件号	DESCRIPTION 描述
1291888-L3	思绪花纹, L3
1291888-L4	梅玛花纹, L4
1291888-L5	晨雾花纹, L5
1291888-L8	繁星花纹, L8
1291888-L9	丝雨花纹, L9
1291888-MZ	镜面玻璃, MZ
1291888-CI	镜面繁星花纹, CI
1291888-EL	镜面银河花纹, EL
1291888-GB	金色夏宫花纹, GB
1291888-C	超净玻璃, C
1291888-GR-NA	墨韵灰, GR
1291888-TA-NA	琥珀棕, TA
1291888-BSZ-NA	金色臻彩绘印图案小, BSZ
1291888-BMZ-NA	金色臻彩绘印图案中, BMZ
1291888-BLZ-NA	金色臻彩绘印图案大, BLZ
1291888-GSZ-NA	灰色臻彩绘印图案小, GSZ
1291888-GMZ-NA	灰色臻彩绘印图案中, GMZ
1291888-GLZ-NA	灰色臻彩绘印图案大, GLZ

Table for IC glass
 IC玻璃选项参考表

P/N 零件号	DESCRIPTION 描述
1291888-GG-NA	烟云灰, GG
1291888-GA-NA	旭日金, GA