



Composed®

Moving panel shower door
K-706080-ML

Features

- Combines with K-70608-FL fixed panel to create complete K-706080-L shower door.
- CleanCoat® technology creates a protective barrier that repels water, prevents dirt and minerals from collecting, and makes it easier to remove hard water spots.

Material

- Frameless, heavy 3/8" (10 mm) thick Crystal Clear tempered glass moving panel.
- Anodized aluminum prevents rust and corrosion.

Installation

- 78" (1981 mm) high.
- For residential use only.
- Not for use in hospitality.

Recommended Products/Accessories

K-23723 Faucet cleaner



Codes/Standards

CPSC 16CFR 1201
ANSI Z97.1

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	SHP	Bright Polished Silver

Available Glass Options

Code	Description
L	Crystal Clear



Composed®
Moving panel shower door
K-706080-ML

Technical Information

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - 44-5/8" (1134 mm)
Min:

Opening Width - 47-7/8" (1216 mm)
Max:

Walk-through - Min: 17" (432 mm)

Walk-through - Max: 19-11/16" (500 mm)

Base-To-Wall 3/8" (10 mm)

Radius – Max:

Glass thickness: 3/8" (10 mm)

Glass coating: CleanCoat®

Notes

The vertical opening should be a minimum of 80" (2032 mm) to allow for installation clearance.