



# Ensemble™

60" x 30" Vikrell® bath, left above-floor drain and liner  
71171112-LNR

## Features


- Designed with a 18-3/4" apron
- Durable high-gloss finish provides a smooth, shiny surface that is easy to clean
- Gently sloping bath with integral apron
- 2" wainscot allows tile-down installation above bath deck
- Includes removable liner to protect bathtub during construction

## Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

## Recommended Products/Accessories

K-23726 Drain treatment



## Codes/Standards

CSA B45.5/IAPMO Z124  
ASTM E162  
ASTM E662  
ADA  
ICC/ANSI A117.1  
OBC  
HUD, UM Bulletin 73

## STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

| Color | Code | Description |
|-------|------|-------------|
|-------|------|-------------|


|                                                                                     |   |       |
|-------------------------------------------------------------------------------------|---|-------|
|  | 0 | White |
|-------------------------------------------------------------------------------------|---|-------|

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

8-27-2026 10:41 - US/CA



## Technical Information

All product dimensions are nominal.

|                        |                              |
|------------------------|------------------------------|
| Drain location:        | Left                         |
| Basin area, bottom:    | 45" x 20" (1143 mm x 508 mm) |
| Basin area, top:       | 53" x 23" (1346 mm x 584 mm) |
| Water depth:           | 11-1/4" (286 mm)             |
| Water capacity:        | 44 gal (166.6 L)             |
| Minimum flat for door: | 2-3/4" (70 mm)               |
| Maximum door width:    | 57-11/16" (1465 mm)          |

## Notes

Install this product according to the installation instructions.

Studs should be positioned roughly as shown. Double-studding is recommended for pivot shower door installations.

Measure your actual product for roughing-in details.

ADA, OBC compliant when installed to the specific requirements of these regulations.