



Ensemble™ Medley®

60" x 32" Vikrell® bath/shower with Aging in Place
backerboards, right above-floor drain
71320128



Features

- 20" apron
- Tongue-and-groove walls with snap-together installation
- High-gloss walls
- Corner shelves
- 3" (76 mm) drain-to-floor clearance for above-floor drain installation
- Aging in Place backerboards
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

Installation

- Alcove
- Right drain
- Caulk-free installation

Recommended Products/Accessories

K-23726 Drain treatment

Included Components

71324106 60" x 32" Vikrell® bath/shower wall set with Aging in Place backerboards

71121122 60" x 32" Vikrell® bath, right above-floor drain



Codes/Standards

CSA B45.5/IAPMO Z124

ASTM E162

ASTM E662

HUD, UM Bulletin 73

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	0	White
---	---	-------


1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

6-21-2026 19:51 - US/CA

Ensemble™ Medley®
60" x 32" Vikrell® bath/shower with Aging in Place
backerboards, right above-floor drain
71320128



Technical Information

All product dimensions are nominal.

Drain location:	Right
Basin area, bottom:	42" x 20" (1067 mm x 508 mm)
Basin area, top:	54" x 26" (1372 mm x 660 mm)
Water depth:	13" (330 mm)
Water capacity:	51 gal (193.1 L)
Minimum flat for door:	3" (76 mm)
Maximum door height:	56-3/4" (1441 mm)
Maximum door width:	57-11/16" (1465 mm)

Notes

Install this product according to the installation instructions.

Studs should be positioned roughly as shown.

Double studding is recommended for pivot shower door installations.