



Features

- Three-piece tongue-and-groove walls with snap-together installation
- High-gloss walls
- Corner shelves
- Must be installed with Ensemble bath or whirlpool (71121110, 71121112, 71121120, 7112122, 76121110 or 76121120)
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

Material


- Made from solid Vikrell® material for strength, durability, and lasting beauty

Installation

- Caulk-free installation

Recommended Products/Accessories

- 5425-59 Frameless sliding bath door
- 5900-59 Framed sliding bath door
- 5905-59 Framed sliding bath door
- 5906-59 Framed sliding bath door, 56-1/4" H x 59-3/8" W
- 542808-59 55-1/2" H frameless sliding bath door with 5/16"-thick glass
- 581005-59 Frameless sliding bath door
- 80001012 12" straight grab bar
- 80001018 18" straight grab bar



Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	0	White
--	---	-------



Medley®
60" x 32" Vikrell® bath/shower wall set
71324100

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Maximum door height: 53-3/4" (1365 mm)

Maximum door width: 57-11/16" (1465 mm)

Notes

Install this product according to the installation instructions.