



Features

- Tongue-and-groove walls with snap-together installation
- High-gloss walls
- Molded-in shelves
- Must be installed with Ensemble bath (71171110, 71171120, 71171112 or 71171122)
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

Installation


- Caulk-free installation

Required Products/Accessories

- 71601110 60" x 30" Vikrell® alcove bath, left drain
- or
- 71601120 60" x 30" Vikrell® alcove bath, right drain
- or
- 71601112 60" x 30" above-floor-drain Vikrell® alcove bath, left drain
- or
- 71601122 60" x 30" above-floor-drain Vikrell® alcove bath, right drain
- or
- 71171110 60" x 30" Vikrell® bath, left drain
- or
- 71171122 60" x 30" Vikrell® bath, right above-floor drain
- or
- 71171120 60" x 30" Vikrell® bath, right drain
- or
- 71171112 60" x 30" Vikrell® bath, left above-floor drain

Recommended Products/Accessories

- 5425-59 Frameless sliding bath door
- 5900-59 Framed sliding bath door
- 5905-59 Framed sliding bath door
- 5906-59 Framed sliding bath door, 56-1/4" H x 59-3/8" W
- 542808-59 55-1/2" H frameless sliding bath door with 5/16"-thick glass
- 581005-59 Frameless sliding bath door
- 80001012 12" straight grab bar
- 80001018 18" straight grab bar



Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	0	White
--	---	-------



Medley®
60" x 30" Vikrell® bath/shower wall set
71374100

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Weight: 66 lbs (29.9 kg)

Maximum door width: 57-11/16" (1465 mm)

Notes

Install this product according to the installation instructions.