



STORE+®

60" x 30" Vikrell® bath/shower with Aging in Place backerboards, right above-floor drain 71470128



Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Includes four rimmed shelves, two caddies, two hooks, and two soap dishes with towel bar
- Dishwasher-safe shelves and bins snap into place; no tools required
- Holds up to 30 bottles
- Easy-to-clean, durable high-gloss finish
- Factory-installed Aging in Place backerboards for future grab bar installation
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

Material

- Compression-molded from our exclusive solid Vikrell® material

Installation

- Alcove
- Caulk-free installation
- Above-floor-drain (AFD) rough-in
- Right drain

Recommended Products/Accessories

K-23726 Drain treatment

Included Components

71171122 60" x 30" Vikrell® bath, right above-floor drain
71474106 60" x 30" Vikrell® bath/shower wall set with Aging in Place backerboards



Codes/Standards

CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
HUD, UM Bulletin 73

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.


Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	0	White
---	---	-------

60" x 30" Vikrell® bath/shower with Aging in Place
backerboards, right above-floor drain
71470128



Technical Information

All product dimensions are nominal.

Drain location:	Right
Basin area, bottom:	45" x 20" (1143 mm x 508 mm)
Basin area, top:	53" x 23" (1346 mm x 584 mm)
Weight:	126.5 lbs (57.4 kg)
Water depth:	11-1/4" (286 mm)
Water capacity:	44 gal (166.6 L)
Minimum flat for door:	2-3/4" (70 mm)
Maximum door height:	56-3/4" (1441 mm)
Maximum door width:	57-11/16" (1465 mm)

Notes

Install this product according to the installation instructions.

Studs should be positioned roughly as shown.

Double studding is recommended for pivot shower door installations.

Felt pad not required for installation.