



# Traverse®

## 60" x 32" Vikrell® bath/shower wall set

### 71524800

#### Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Modern subway tile design
- Full-length shelf provides generous storage
- Easy-to-clean, durable high-gloss finish
- Includes complete wall set
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

#### Material

- Compression-molded from our exclusive solid Vikrell® material

#### Installation

- Pro4™ installation system features a two-piece back wall design, enabling one-person handling and installation
- Alcove
- Caulk-free installation

#### Recommended Products/Accessories

- 71121112 60" x 32" Vikrell® bath, left above-floor drain
- 71121122 60" x 32" Vikrell® bath, right above-floor drain



#### Codes/Standards

CSA B45.5/IAPMO Z124  
ASTM E162  
ASTM E662

#### STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

#### Available Colors/Finishes

*Color tiles intended for reference only.*

#### Color Code Description

|                                                                                     |   |       |
|-------------------------------------------------------------------------------------|---|-------|
|  | 0 | White |
|-------------------------------------------------------------------------------------|---|-------|

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

8-27-2026 10:55 - US/CA



**Requires Bath 71121810 (Shown) or 71121820**

**Drain Detail**

5-3/4" (146 mm)

15-1/4" (387 mm)

2-3/4" (70 mm)

60" (1524 mm)

33-1/4" (845 mm)

22-1/2" (572 mm)

16" (406 mm)

30" (762 mm)

14" (356 mm)

6" (152 mm) (Typical)

8-1/2" (216 mm)

15-1/2" (394 mm)

8" (203 mm)

4" (102 mm)

32" (813 mm)

1-1/4" (32 mm)

8-1/2" (216 mm)

3-1/2" (89 mm)

60-1/8" (1527 mm) Min

60-1/4" (1530 mm) Max

57-1/16" (1449 mm)

2" (51 mm)

77-1/16" (1957 mm)

21" (533 mm)

20" (508 mm)

18" (457 mm)

60" (1524 mm)

Ø 2" (51 mm) Drain

Drain Cutout

|                      |                   |
|----------------------|-------------------|
| Weight:              | 60 lbs (27.2 kg)  |
| Maximum door height: | 58-3/4" (1492 mm) |
| Maximum door width:  | 57-3/4" (1467 mm) |

Install this product according to the installation instructions.

Left drain model is shown. Right drain model is a mirror of the left drain model.