



# Forum™ Traverse®

60" x 30" above-floor-drain Vikrell® bath/shower, right drain

**71600122**



## Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Modern subway tile design
- Full-length shelf provides generous storage
- Easy-to-clean, durable high-gloss finish
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

## Material

- Compression-molded from our exclusive solid Vikrell® material

## Installation

- Pro4™ installation system features a two-piece back wall design, enabling one-person handling and installation
- Alcove
- Caulk-free installation
- Right drain
- Above-floor-drain (AFD) rough-in

## Included Components

- 71574100 60" x 30" Vikrell® bath/shower wall set
- 71601122 60" x 30" above-floor-drain Vikrell® alcove bath, right drain



## Codes/Standards

CSA B45.5/IAPMO Z124  
ASTM E162  
ASTM E662  
HUD, UM Bulletin 73

## STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty


See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

| Color | Code | Description |
|-------|------|-------------|
|-------|------|-------------|

|                                                                                     |   |       |
|-------------------------------------------------------------------------------------|---|-------|
|  | 0 | White |
|-------------------------------------------------------------------------------------|---|-------|



### Technical Information

All product dimensions are nominal.

|                        |                    |
|------------------------|--------------------|
| Drain location:        | Right              |
| Weight:                | 127 lbs (57.6 kg)  |
| Water depth:           | 11-1/4" (286 mm)   |
| Water capacity:        | 41.9 gal (158.6 L) |
| Minimum flat for door: | 2-3/4" (70 mm)     |
| Maximum door height:   | 56-3/4" (1441 mm)  |
| Maximum door width:    | 57-5/8" (1464 mm)  |

### Notes

Install this product according to the installation instructions.