



Forum™ Medley®

60" x 30" above-floor-drain Vikrell® bath/shower, left drain

71700112



Features

- Tongue-and-groove walls with snap-together installation
- Molded-in shelves
- Easy-to-clean, durable high-gloss finish
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

Installation

- Alcove
- Left drain
- Caulk-free installation
- Above-floor-drain (AFD) rough-in

Included Components

- 71374100 60" x 30" Vikrell® bath/shower wall set
- 71601112 60" x 30" above-floor-drain Vikrell® alcove bath, left drain



Codes/Standards

CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
HUD, UM Bulletin 73

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Drain location:	Left
Basin area, bottom:	45" x 20" (1143 mm x 508 mm)
Basin area, top:	53" x 23" (1346 mm x 584 mm)
Weight:	123.5 lbs (56 kg)
Water depth:	11-1/4" (286 mm)
Water capacity:	45.5 gal (172.2 L)
Minimum flat for door:	2-3/4" (70 mm)
Maximum door height:	54-3/4" (1391 mm)
Maximum door width:	57-11/16" (1465 mm)

Notes

Install this product according to the installation instructions.