



# Forum™ Medley®

60" x 30" Vikrell® bath/shower, right drain  
71700120



## Features

- Tongue-and-groove walls with snap-together installation
- Molded-in shelves
- Easy-to-clean, durable high-gloss finish
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

## Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

## Installation

- Alcove
- Right drain
- Caulk-free installation

## Included Components

- 71374100 60" x 30" Vikrell® bath/shower wall set
- 71601120 60" x 30" Vikrell® alcove bath, right drain



## Codes/Standards

CSA B45.5/IAPMO Z124  
ASTM E162  
ASTM E662

## STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty


See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

| Color | Code | Description |
|-------|------|-------------|
|-------|------|-------------|

|                                                                                     |   |       |
|-------------------------------------------------------------------------------------|---|-------|
|  | 0 | White |
|-------------------------------------------------------------------------------------|---|-------|



### Technical Information

All product dimensions are nominal.

|                        |                              |
|------------------------|------------------------------|
| Drain location:        | Right                        |
| Basin area, bottom:    | 45" x 20" (1143 mm x 508 mm) |
| Basin area, top:       | 53" x 23" (1346 mm x 584 mm) |
| Weight:                | 121 lbs (54.9 kg)            |
| Water depth:           | 12-1/4" (311 mm)             |
| Water capacity:        | 48.9 gal (185.1 L)           |
| Minimum flat for door: | 2-3/4" (70 mm)               |
| Maximum door height:   | 54-3/4" (1391 mm)            |
| Maximum door width:    | 57-11/16" (1465 mm)          |

### Notes

Install this product according to the installation instructions.