



Forum™ STORE+®

60" x 30" above-floor-drain Vikrell® bath/shower, left drain

71800112



Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Includes four rimmed shelves, two caddies, two hooks, and two soap dishes with towel bar
- Dishwasher-safe shelves and bins snap into place; no tools required
- Holds up to 30 bottles
- Easy-to-clean, durable high-gloss finish
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

Installation

- Alcove
- Left drain
- Above-floor-drain (AFD) rough-in
- Caulk-free installation

Recommended Products/Accessories

- 5425-59 Frameless sliding bath door
- 5905-3G05 Sliding bath door, 56-1/4" H x 59-3/8" W
- 5906-59 Framed sliding bath door, 56-1/4" H x 59-3/8" W

Included Components

- 71474100 60" x 30" Vikrell® bath/shower wall set
- 71601112 60" x 30" above-floor-drain Vikrell® alcove bath, left drain



Codes/Standards

CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
HUD, UM Bulletin 73

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Drain location:	Left
Weight:	123 lbs (55.8 kg)
Water depth:	11-1/4" (286 mm)
Water capacity:	45.5 gal (172.2 L)
Minimum flat for door:	2-3/4" (70 mm)
Maximum door height:	57" (1448 mm)
Maximum door width:	57-11/16" (1465 mm)

Notes

Install this product according to the installation instructions.