



Forum™ STORE+®

60" x 32" Vikrell® bath/shower, right drain
71810120



Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Includes four rimmed shelves, two caddies, two hooks, and two soap dishes with towel bar
- Dishwasher-safe shelves and bins snap into place; no tools required
- Holds up to 30 bottles
- Easy-to-clean, durable high-gloss finish
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

Installation

- Alcove
- Right drain
- Caulk-free installation

Included Components

- 71424100 60" x 32" Vikrell® bath/shower wall set
- 71611120 60" x 32" Vikrell® alcove bath, right drain



Codes/Standards

CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes



Color tiles intended for reference only.

Color Code Description

	0	White
---	---	-------



 Recommended Support
Clip Location (5 Total)



Technical Information

All product dimensions are nominal.

Drain location:	Right
Weight:	126.3 lbs (57.3 kg)
Water depth:	13-1/4" (337 mm)
Water capacity:	55.8 gal (211.2 L)
Minimum flat for door:	2-3/4" (70 mm)
Maximum door height:	57" (1448 mm)
Maximum door width:	57-11/16" (1465 mm)

Notes

Install this product according to the installation instructions.