



Accord®

48" x 36" Vikrell® seated shower with Aging in Place backerboards, center drain

72280106



Features

- 3-1/2" (89 mm) threshold
- Durable high-gloss finish
- Pivot snap-together modular design
- Removable seat
- Aging in Place backerboards

Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

Installation

- Alcove
- Center drain
- Caulk-free installation

Recommended Products/Accessories

- 5475-48 Frameless sliding shower door
- 5970-48 Framed sliding shower door
- 5975-48 Framed sliding shower door
- 5976-48 Framed sliding shower door
- 547808-48 Frameless sliding shower door
- 581075-48 Frameless sliding shower door
- 80001018 18" straight grab bar
- 80001024 24" straight grab bar
- K-23726 Drain treatment
- 80012222 22" curved grab bar

Included Components

- 72281100 48" x 36" Vikrell® seated shower base, center drain
- 72284106 48" x 36" Vikrell® seated shower wall set with Aging in Place backerboards



Codes/Standards

- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description


	0	White
---	---	-------

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

6-21-2026 20:38 - US/CA



Technical Information

All product dimensions are nominal.

Drain location:	Center
Weight:	133 lbs (60.3 kg)
Minimum flat for door:	3-1/4" (83 mm)
Maximum door height:	70-5/8" (1794 mm)
Maximum door width:	44-5/8" (1133 mm)

Notes

Install this product according to the installation instructions.

Base cannot be installed without the wall surround.

Studs should be positioned roughly as shown.

Double studding is recommended for pivot shower door installations.