



# Ensemble™ Curve

42" x 34" Vikrell® shower, center drain  
72350100



## Features

- Tongue-and-groove walls with snap-together installation
- Smooth, curved wall design
- Convenient shelves, shaving ledge/footrest
- Full-length water-containment guard and 1" (25 mm) weep channels redirect water into the base, providing four-sided water containment
- Textured bottom surface
- 4-3/4" (121 mm) threshold
- Easy-to-clean, durable high-gloss finish
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

## Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

## Installation

- Alcove
- Center drain
- Caulk-free installation

## Recommended Products/Accessories

K-23726 Drain treatment

## Included Components

72351100 42" x 34" Vikrell® shower base, center drain  
72352100 42" Vikrell® shower back wall  
72345100 34" Vikrell® shower end wall set



## Codes/Standards

CSA B45.5/IAPMO Z124  
ASTM E162  
ASTM E662  
HUD, UM Bulletin 73

## STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.


## Available Colors/Finishes

*Color tiles intended for reference only.*

### Color Code Description

|                                                                                     |   |       |
|-------------------------------------------------------------------------------------|---|-------|
|  | 0 | White |
|-------------------------------------------------------------------------------------|---|-------|

**Ensemble™ Curve**  
42" x 34" Vikrell® shower, center drain  
**72350100**



**Technical Information**

All product dimensions are nominal.

|                        |                   |
|------------------------|-------------------|
| Drain location:        | Center            |
| Weight:                | 105 lbs (47.6 kg) |
| Minimum flat for door: | 3" (76 mm)        |
| Maximum door height:   | 70-1/2" (1791 mm) |
| Maximum door width:    | 38-5/8" (981 mm)  |

**Notes**

Install this product according to the installation instructions.