

WALL-MOUNT SHOWER FAUCET K-72351T

Features

- Brass construction
- Includes hand shower with bracket
- G1/2" thread connection
- Water efficient flow control
- Easy clean spray nozzles
- Ergonomic grip and use

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552


Installation Notes

Install this product according to the installation guide.



Specified Model


Model	Description	Color/Finished
K-72351T-4	Aleo wall-mount shower faucet	CP



Flow Curve

Note: Flow rates are approximate. (1 liter = 3.785 gallon, 1 bar = 14.5 psi)

Dimensions are approximate.
Unit: mm



Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- พร้อมฝักบัวสายอ่อนพร้อมขอแขวน
- เกลียวข้อต่อมาตรฐานขนาด G1/2"
- กระแสน้ำคงที่
- ทำความสะอาดง่าย
- มีข้อจับถูกต้องตามหลักสรีรศาสตร์

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- มอก. 2066-2552

ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งสุขภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

ก๊อกผสมเย็นอาบแบบติดผนัง พร้อมฝักบัวสายอ่อน K-72351T



รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-72351T-4	ก๊อกผสมเย็นอาบแบบติดผนังพร้อมฝักบัวสายอ่อน รุ่น อาเลโอ	CP




กราฟแสดงอัตราการไหล

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 ลิตร = 3.785 แกลลอน, 1 บาร์ = 14.5 psi)

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



ภาพแสดงผลิตภัณฑ์