



Ensemble™ Curve

48" x 34" Vikrell® shower with Aging in Place backerboards, center drain

72360106



Features

- 3-1/8" (79 mm) threshold
- Easy-to-clean, durable high-gloss finish
- Three-piece tongue-and-groove walls with snap-together installation
- Modular design allows it to be moved around corners and through doorways with ease
- Curved wall design for a smooth look and feel
- Convenient shelves provide generous storage space
- Shaving ledge/footrest for added comfort
- Factory-installed Aging in Place backerboards for future grab bar installation

Material

- Compression-molded from our exclusive solid Vikrell® material

Installation

- Alcove
- Center drain
- Caulk-free installation

Recommended Products/Accessories

- 5475-48 Frameless sliding shower door
- 547808-48 Frameless sliding shower door
- 581075-48 Frameless sliding shower door
- 5960-48 Framed sliding shower door
- 80001018 18" straight grab bar
- 80001036 36" straight grab bar

Included Components

- 72321100 48" x 34" Vikrell® shower base, center drain
- 72345106 34" Vikrell® shower end wall set with Aging in Place backerboards
- 72362106 48" Vikrell® shower back wall with Aging in Place backerboards



Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	0	White
---	---	-------


1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

6-21-2026 20:30 - US/CA

Ensemble™ Curve
48" x 34" Vikrell® shower with Aging in Place
backerboards, center drain
72360106



Technical Information

All product dimensions are nominal.

Drain location:	Center
Weight:	126.6 lbs (57.4 kg)
Minimum flat for door:	2-1/2" (64 mm)
Maximum door height:	70-1/2" (1791 mm)
Maximum door width:	44-5/8" (1134 mm)

Notes

Install this product according to the installation instructions.