



Medley®
36" x 34" Vikrell® shower with Aging in Place
backerboards, center drain
72400106



Features

- 3-1/8" (79 mm) threshold
- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Smooth wall design with molded-in shelves and shaving ledges
- Easy-to-clean, durable high-gloss finish

Material

- Compression-molded from our exclusive solid Vikrell® material

Installation

- Alcove
- Center drain
- Caulk-free installation

Recommended Products/Accessories

80001012 12" straight grab bar
80001018 18" straight grab bar
80001024 24" straight grab bar
K-23726 Drain treatment

Included Components

72301100 36" x 34" Vikrell® shower base, center drain
72402100 36" Vikrell® shower back wall
72405106 34" Vikrell® shower end wall set with Aging in Place backerboards



Codes/Standards

CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
HUD, UM Bulletin 73

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description




	0	White
---	---	-------

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

6-21-2026 20:32 - US/CA



Note: Right and left end walls are the same, only mirrored.

□ □ Backer board locations

Technical Information

All product dimensions are nominal.

Drain location:	Center
Weight:	99 lbs (44.9 kg)
Minimum flat for door:	2-1/2" (64 mm)
Maximum door height:	70-3/4" (1797 mm)
Maximum door width:	33-5/8" (854 mm)

Notes

Install this product according to the installation instructions.

Attach grab bars at the specified backerboard locations only.

Studs should be positioned roughly as shown.