



**Medley®**  
48" x 34" Vikrell® shower, center drain  
**72410100**



**Features**

- 3-1/8" (79 mm) threshold
- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Smooth wall design with molded-in shelves and shaving ledges
- Easy-to-clean, durable high-gloss finish

**Material**

- Compression-molded from our exclusive solid Vikrell® material

**Installation**

- Alcove
- Center drain
- Caulk-free installation

**Recommended Products/Accessories**

5475-48 Frameless sliding shower door  
5970-48 Framed sliding shower door  
5975-48 Framed sliding shower door  
5976-48 Framed sliding shower door  
547808-48 Frameless sliding shower door  
581075-48 Frameless sliding shower door  
80001012 12" straight grab bar  
80001018 18" straight grab bar  
80001024 24" straight grab bar  
72186104 Freestanding shower seat  
K-23726 Drain treatment

**Included Components**

72321100 48" x 34" Vikrell® shower base, center drain  
72412100 48" Vikrell® shower back wall  
72405100 34" Vikrell® shower end wall set



**Codes/Standards**

CSA B45.5/IAPMO Z124  
ASTM E162  
ASTM E662  
HUD, UM Bulletin 73

**STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty**



See website for detailed warranty information.

**Available Colors/Finishes**

*Color tiles intended for reference only.*

**Color Code Description**

|                                                                                     |   |       |
|-------------------------------------------------------------------------------------|---|-------|
|  | 0 | White |
|-------------------------------------------------------------------------------------|---|-------|



### Technical Information

All product dimensions are nominal.

|                        |                   |
|------------------------|-------------------|
| Drain location:        | Center            |
| Weight:                | 110 lbs (49.9 kg) |
| Minimum flat for door: | 2-1/2" (64 mm)    |
| Maximum door height:   | 70-3/4" (1797 mm) |
| Maximum door width:    | 45-5/8" (1159 mm) |

### Notes

Install this product according to the installation instructions.

Studs should be positioned roughly as shown.

Double studding is recommended for pivot shower door installations.