



Medley®

60" x 34" Vikrell® shower with Aging in Place backerboards, center drain

72430106



Features

- 3-1/8" (79 mm) threshold
- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Smooth wall design with molded-in shelves and shaving ledges
- Easy-to-clean, durable high-gloss finish
- Factory-installed Aging in Place backerboards for future grab bar installation

Material

- Compression-molded from our exclusive solid Vikrell® material

Installation

- Alcove
- Center drain
- Caulk-free installation

Recommended Products/Accessories

5475-59 Frameless sliding shower door
5970-59 Framed sliding shower door
5975-59 Framed sliding shower door
5976-59 Framed sliding shower door
547808-59 Frameless sliding shower door
581075-59 Frameless sliding shower door
80001012 12" straight grab bar
80001018 18" straight grab bar
80001024 24" straight grab bar
72186104 Freestanding shower seat
K-23726 Drain treatment

Included Components

72331100 60" x 34" Vikrell® shower base, center drain
72432106 60" Vikrell® shower back wall with Aging in Place backerboards
72405106 34" Vikrell® shower end wall set with Aging in Place backerboards



Codes/Standards

CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
HUD, UM Bulletin 73

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Drain location:	Center
Weight:	136.5 lbs (61.9 kg)
Minimum flat for door:	2-1/2" (64 mm)
Maximum door height:	70-3/4" (1797 mm)
Maximum door width:	57-5/8" (1464 mm)

Notes

Install this product according to the installation instructions.

Studs should be positioned roughly as shown. Attach grab bars at the specified backer board locations only.