



# Medley®

## 60" x 30" Vikrell® shower with Aging in Place backerboards, left drain 72440116



### Features

- 4" threshold
- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Smooth wall design with molded-in shelves and shaving ledges
- Easy-to-clean, durable high-gloss finish
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

### Material

- Compression-molded from our exclusive solid Vikrell® material

### Installation

- Alcove
- Left drain
- Caulk-free installation

### Recommended Products/Accessories

- 80001012 12" straight grab bar
- 80001018 18" straight grab bar
- 80001024 24" straight grab bar
- K-23726 Drain treatment
- 547909-59 Sliding shower door
- 547808-59 Frameless sliding shower door
- 581075-59 Frameless sliding shower door
- 5475-59 Frameless sliding shower door
- 5960-59 Framed sliding shower door

### Included Components

- 72171110 60" x 30" Vikrell® shower base, left drain
- 72432106 60" Vikrell® shower back wall with Aging in Place backerboards
- 72445106 30" Vikrell® shower end wall set with Aging in Place backerboards



### Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73

### STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

#### Color Code Description


|                                                                                     |   |       |
|-------------------------------------------------------------------------------------|---|-------|
|  | 0 | White |
|-------------------------------------------------------------------------------------|---|-------|

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

6-21-2026 20:31 - US/CA



### Technical Information

All product dimensions are nominal.

|                        |                   |
|------------------------|-------------------|
| Drain location:        | Left              |
| Weight:                | 134 lbs (60.8 kg) |
| Minimum flat for door: | 3" (76 mm)        |
| Maximum door height:   | 70-3/4" (1797 mm) |
| Maximum door width:    | 57-5/8" (1464 mm) |

### Notes

Install this product according to the installation instructions.

Studs should be positioned roughly as shown. Attach grab bars at the specified backerboard locations only.