



Medley®
36" x 36" Vikrell® shower, center drain
72450100



Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Smooth wall design with molded-in shelves and shaving ledges
- Full-length water-containment guard and 1" (25 mm) weep channels redirect water into the base, providing four-sided water containment
- Textured bottom surface
- 3-13/16" (97 mm) threshold
- Easy-to-clean, durable high-gloss finish
- Innovative Dry-Block™ seal and channeled water containment system form watertight seams

Material

- Compression-molded from our exclusive solid Vikrell® material

Installation

- Alcove
- Center drain
- Caulk-free installation

Included Components

- 72061100 36" x 36" Vikrell® shower base, center drain
- 72402100 36" Vikrell® shower back wall
- 72485100 36" Vikrell® shower end wall set



Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	0	White
---	---	-------



Technical Information

All product dimensions are nominal.

Drain location: Center

Weight: 103 lbs (46.7 kg)

Notes

Install this product according to the installation instructions.